





CATEGORY	DESCRIPTION	P/N #
CONNECTOR	RJ45 8P8C 全塑带灯	MJ5688-XX11-GRNLX

REV.	ECN NO	DESCRIPTION	REVISED	DATE
A01	—	New Release	XSY	2015.01.16
A02	—	修正PCB LAYOUT	XSY	2015.07.09


REV.	ECN NO	DESCRIPTION	REVISED	DATE
A01	—	New Release	XSY	2015.01.16
A02	—	修正PCB LAYOUT	XSY	2015.07.09

SPECIFICATION

1. VOLTAGE RATING: 150 VAC RMS.
2. CURRENT RATING: 1.5 AMP
3. CONTACT RESISTANCE: 40 mΩ MAX
4. INSULATION RESISTANCE: 500MΩ MIN.
5. WITHSTAND VOLTAGE: AC1000V RMS 60s.
6. OPERATING TEMPERATURE: -40°C~+80°C



Recommend PCB Layout
(Jack Top View)
Tolerance: ±0.05mm
Recommend PCB Thickness: 1.6mm



MJ5688-XX11-GRNLX

X	LED-L	LED-R
1	Green	Yellow
2	Yellow	Green

Table 3

X	Terminal Plating
0	Au 1u" Plating
1	Au 3u" Plating
2	Au 6u" Plating
3	Au 15u" Plating

Table 2

X	Housing Color	Housing Material
B	Black	
U	Blue	PBT UL94V-0
Y	Yellow	
1	Black	
2	Blue	PA9T UL94V-0
3	Yellow	

Table 1

d	LED-R	1	SEE TABLE 3	Tin PLATING	
c	LED-L	1	SEE TABLE 3	Tin PLATING	
b	TERMINAL	8	PHOSPHOR BRONZE φ0.46mm	SEE TABLE 2	
a	HOUSING	1	SEE TABLE 1	SEE TABLE 1	
NO.	PART NAME	QTY	MATERIAL	PLATING & COLOR	Remark

d	LED-R	1	SEE TABLE 3	Tin PLATING	
c	LED-L	1	SEE TABLE 3	Tin PLATING	
b	TERMINAL	8	PHOSPHOR BRONZE φ0.46mm	SEE TABLE 2	
a	HOUSING	1	SEE TABLE 1	SEE TABLE 1	
NO.	PART NAME	QTY	MATERIAL	PLATING & COLOR	Remark

UNLESS OTHERWISE SPECIFIED TOLERANCES	DECIMALS:	ANGLES:
	X : ±0.5	X : ±2°
	XX : ±0.3	XX : ±1°
	XXX : ±0.2	


东莞市合陵电子有限公司
 DongGuan Heling Electronic Co.,LTD
 Connector

SCALE: 1/1	UNIT: mm	DWG. NO:
SIZE: A3	PAGE: 1 OF 1	WI-061-064
APPROVED BY	CHECKED BY	PREPARED BY
DICK	XSY	XSY
CUSTOMER COPY		