


CATEGORY	DESCRIPTION	P/N #
CONNECTOR	RJ45 8P8C DIP塑沉板H=8.80mm	MJ88H-BX11-HLRV1-1X

REV.	ECN NO	DESCRIPTION	REVISED	DATE
A01		New Release	XSY	2018.07.26




MJ88H-BX11-HLRV1-1X




X	Terminal Plating
0	Contacts Area: Au 1u"
1	Solder Area: Bright-Tin 80u"
2	Contacts Area: Au 6u"
3	Solder Area: Bright-Tin 80u"
6	Contacts Area: Au 15u"
	Solder Area: Bright-Tin 80u"
	Au 1u" Overfill(全塗)

X	包裝方式
C	卷帶包裝
P	吸塑盒包裝

- SPECIFICATION
- CURRENT RATING: 1.5AMPS
  - VOLTAGE RATING: 125V AC
  - INSULATION RESISTANCE: 500MΩ MIN.
  - WITHSTAND VOLTAGE: AC1000V RMS 50Hz or 60Hz MIN.
  - CONTACT RESISTANCE: 30mΩ MAX.
  - DURABILITY: 750 MATING CYCLES
  - OPERATING TEMPERATURE: -25°C~+80°C



Recommend PCB Layout  
Jack Top View  
Tolerance: ±0.05mm



c	SHELL	1	BRASS	NI PLATING
b	TERMINAL	8	PHOSPHOR BRONZE	SEE TABLE 1
a	HOUSING	1	LCP+30%G.F UL94V-0	BLACK
NO.	PART NAME	QTY	MATERIAL	PLATING & COLOR
				Remark

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS: ANGLES:

X.X : ±0.30 X : ±2°

X.XX : ±0.20 X.X : ±1°

X.XXX : ±0.10

SCALE: 1/1 UNIT: mm DWG. NO:

SIZE: A3 PAGE: 1 OF 1 REV: A01

APPROVED BY: XSY CHECKED BY: XSY PREPARED BY: XSY

DICE

CUSTOMER COPY

 東莞市合陵電子有限公司  
Dongguan Heling Electronic Co., LTD