





CATEGORY	DESCRIPTION	P/N #
CONNECTOR	RJ45 SMT TYPE H12.5 全塑无灯	MJ56881-XX11-HXRN1-X

REV.	ECN NO	DESCRIPTION	REVISED	DATE
A01		New Release	XSY	2016.07.08
A02		塑胶增加颜色选项	XSY	2018.04.29



- Specifications:
1. Rated Current: 1.5A
 2. Contact resistance: 40mΩ MAX.
 3. Insulation resistance: 500MΩ MIN.
 4. Dielectric withstand: 500V AC for 1 minute
 5. Operating temperature: -40°C~+80°C
 6. Insertion/Extraction life: 750 Cycles
 7. To Conform to the "RoHS Directive"
 8. Resistance to reflow Soldering Heat 260°C 10 Seconds



X	Housing Color
B	Black
U	Blue CX018
Y	Yellow 114C

X	Housing Material
L	LCP UL94V-0
8	PA8T UL94V-0

X	包装方式
C	卷带包装
P	吸塑包装

X	Terminal Plating
0	Au 1u" Plating
1	Au 3u" Plating
2	Au 6u" Plating
3	Au 15u" Plating
4	Au 30u" Plating

c	Stator	2	Copper Alloy T=0.20mm	Ni Plating	
b	Terminal	8	Phosphor Bronze T=0.30mm	Au/Wette-Tin Plating	
a	Housing	1	SEE TABLE	SEE TABLE	
NO.	PART NAME	QTY	MATERIAL	PLATING & COLOR	Remark

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS:	ANGLES:
X : ±0.5	X : ±2°
X.X : ±0.3	X.X : ±1°
X.XX : ±0.2	
X.XXX : ±0.1	

东莞市合陵电子有限公司
 Dongguan Heling Electronic Co.,LTD
 Connector

SCALE: 1/1	UNIT: mm	DWG.NO:
SIZE: A3	PAGE: 1 OF 1	REV: A02
APPROVED BY	CHECKED BY	PREPARED BY
DICK	XSY	XSY
CUSTOMER COPY		