



CATEGORY	DESCRIPTION	P/N #
CONNECTOR	RA45 2x2 8P8C 全塑 (十字脚)	MJ5988-XX22-HPRN1


REV.	ECN NO.	DESCRIPTION	REVISED	DATE
A01		New Release	XSY	2017.11.15

- 1.RJ ELECTRICAL CHARACTERISTICS
- 1-1: VOLTAGE: 150V AC RMS
  - 1-2: CURRENT RATING: 1.5A
  - 1-3: CONTACT RESISTANCE: 40mΩ MAX.
  - 1-4: INSULATION RESISTANCE: 500MΩ MIN.
  - 1-5: DIELECTRIC WITHSTANG VOLTAGE : 1000V AC
  - 1-6: OPERATEURE TEMPERATURE: -40°C~80°C



MJ5988-XX22-HPRN1

SEE TABLE 1		SEE TABLE 2	
X	Housing Color	X	Terminal Plating
B	BLACK	0	G/F Plating
Y	YELLOW	1	Au 3u" Plating
U	BLUE	2	Au 6u" Plating
G	GRAY	3	Au 15u" Plating
W	WHITE		



Recommend PCB Layout  
Jack Top View  
Tolerance: ±0.05mm  
Recommend PCB Thickness: 1.6mm

NO.	PART NAME	QTY	MATERIAL	PLATING & COLOR	Remark
a	HOUSING	1	PBT UL94V-0	SEE TABLE 1	
b	COVER	2	PBT UL94V-0	SEE TABLE 1	
c	INSERT 1#	2	PBT UL94V-0	SEE TABLE 1	
d	INSERT 2#	2	PBT UL94V-0	SEE TABLE 1	
e	TERMINAL	32	PHOSPHOR BRONZE Ø0.46	SEE TABLE 2	

UNLESS OTHERWISE SPECIFIED TOLERANCES		DECIMALS:		ANGLES:	
X	: ±0.5	X	: ±2°	X.X	: ±0.3
X.X	: ±0.3	X.X	: ±1°	X.XX	: ±0.2
SCALE: 1/1	UNIT: mm	APPROVED BY	CHECKED BY	PREPARED BY	
SIZE: A3	PAGE: 1 OF 1	DICK	XSY	XSY	
CUSTOMER COPY					

  
**东莞市合陵电子有限公司**  
 Dongguan Heling Electronic Co.,LTD