

P/N:ECT:818000376

SPRING RF CONNECTOR ——弹片系列



技术参数 Technology Parameters

- Frequency Range 频率范围: DC ~ 3GHz
- Impedance 特性阻抗: 50 Ω
- Pre-load Force 承受压力: 0.4N.Min
- Solder Ability 焊接能力: sold coverage 95%
- Center Contact Resistance 接触电阻: 50m Ω Max
- Voltage Standing wave Ratio(VSWR) 电压驻波比: 1.5 Max(DC~3GHz);
- Insertion Loss 插入损耗: -0.6 dB Max(DC~3GHz);
- Mechanical Durability 机械寿命: 100 Cycles
- Operating Temperature 工作温度: -40°C ~ +65°C

Appearance Dimensions 外形尺寸:

