

POLYMER PTC RESETTABLE FUSE




Part Number: TRM055Z-3

1、 Physical Dimensions

Unit:mm

Part Number	A	B	C	D	E	Lead
	Max	Max	TYP	Nor	Max	Φ
TRM055Z-3	14.0	18.0	5.1	18±1	4.5	0.80



Logo
 M 055 Holding Current
 Max.Interrupt voltage
 XX Lot No.

2、 Electrical Characteristics

Part Number	I _H (A)	I _T (A)	V _{max} OP V _{dc}	I _{max} (A)	V _{max} Interrupt V _{rms}	T _{trip} (Max time to trip)		Pd _{typ} (W)	R _{min} (Ω)	R _{max} (Ω)	R1 _{max} (Ω)
						Current(A)	Time(S)				
TRM055Z-3	0.55	1.25	240	7.0	265	2.75	26.0	3.4	1.15	1.35	2.70

I_H: Holding Current: maximum current at which the device will not trip in 25°C still air.

I_T: Tripping Current minimum current at which the device will trip in 25°C still air.

V_{max}: Maximum voltage device can withstand without damage at rated current.

I_{max}: Maximum fault current device can withstand without damage at rated voltage.

T_{trip}: Maximum time to trip(s) at assigned current.

Pd_{typ}: Rated working power.

R_{min}: Minimum resistance of device prior to trip at 25°C.


R_{max}: Maximum resistance of device prior to trip at 25°C.

R1_{max}: Maximum resistance of device is measured one hours post reflow at 25°C.

3、 Thermal Derating

Part Number	Ambient Operating Temperature								
	-40°C	-20°C	0°C	25°C	40°C	50°C	60°C	70°C	85°C
TRM055Z-3	0.87	0.76	0.65	0.55	0.44	0.39	0.33	0.28	0.21

4、 Wave Soldering Parameters



Profile Feature	Condition
Average Ramp-Up Rate (T _{smax} to TP)	4°C/second max.
Preheat	
-Temperature Min (T _{smin})	100°C
-Temperature Max (T _{smax})	125°C
-Time (T _{smin} to T _{smax})	60-180 seconds
Peak Temperature (TP)	265°C
Max Time at Peak Temperature (t _P)	5 seconds
Ramp-Down Rate	6 °C /second max.
Time 25°C to Peak Temperature	5 minutes max.
Storage Condition	0°C ~35°C, ≦ 70%RH, 2 Years

5、 Package Information

Packing quantity:200pcs/bag

6、 Agency Recognition: TUV



Caution: Operation beyond the rated voltage or current may result in rupture electrical arcing or flame. Specifications are subject to change without notice.

TEL: 86-0769-3892 0554 FAX: 86-0769-8793 2077 E-mail: sales@tlcet.com.cn
 Address: No.18, 5th GaoLi Road, TangXia Town, DongGuan, GuangDong, P.R China 523710