


本公司智慧財產，未經同意不得複製
DAILYWELL copyright, may not be used
without permission from DAILYWELL



Model No.	POS.1	POS.2	POS.3
	2TES1	ON	NONE
Term. Comm.	2-3	N/A	2-1
SCHEMATIC			

SWITCH FUNCTION



P.C. MOUNTING



SPECIFICATIONS

CONTACT RATING: Max 0.4 VA max @ 48 VAC or DC
MECHANICAL LIFE: minimum 40,000 operations.
CONTACT RESISTANCE: 50mΩ max.
INSULATION RESISTANCE: 1,000MΩ min.
DIELECTRIC STRENGTH: 500 Vrms min. @ sea level.
OPERATING TEMPERATURE: -20°C to 85°C.
DEGREE OF PROTECTION : IP67 [ⓓ]

MATERIALS

ACTUATOR - Brass,chrome platede, internal O-ring seal.
 Standard for all actuators.
BUSHING & HOUSING - SPCC
CASE - Glass filled nylon 6/6, flame retardant,heat stabilized
 (UL94v-0)
CONTACT/TERMINALS - Phosphor bronze gold - plated over nickel barrier.
TERMINAL SEAL - Epoxy
RoHS & Lead Free

德利威電子股份有限公司
DAILYWELL ELECTRONICS CO.,LTD.

	符號	原尺寸	修改後尺寸	變更日期
1	Ⓐ		圖面更正	NOV-05-2009
2	Ⓑ1	1.09(.043)	1.0(.039)	AUG-03-2010
3	Ⓑ2	26°	28°	AUG-03-2010
4	Ⓒ		增加尺寸標示	MAR-01-2017
5	Ⓓ	30°	20°	AUG-14-2017

SCALE (比例) : 3 : 2
TOLERANCE (公差) :
 0.00 mm ± 0.25mm
 0.0 mm ± 0.40mm
ANGULAR : ± 5°
FILE NAME : 2TESP0002

TITLE 圖名		Subminiature Toggle Switches			SIZE 圖紙
DWG NO. 圖號		2TES1M2RES			UNIT 單位
REV. 版本		E	DATE 日期	DEC - 24 - 2008	SHEET 張數
CHECKED BY 審核		DRAWN BY 製圖		IRENE	1 OF 1