


A-A



B-B

1. 嵌合相手端子型番 : 171662
2. バラ状端子型番 : 173706

1. RECEPTACLE CONTACT PN: 171662
2. L/P CONTACT PN 173706

SELECTIVE GOLD 部分金めっき	SELECTIVE TIN 部分錫めっき	BRASS 黄銅	t0.32 板厚0.32	171661-5	3
SELECTIVE GOLD 部分金めっき	PRE-TIN (0.76μm MIN.) 錫めっき済	BRASS 黄銅	t0.32 板厚0.32	171661-2	2
FINISH 仕上		BRASS 黄銅	t0.32 板厚0.32	171661-1	1
		MATERIAL 材料		PN 型番	ITEM No. 項番

WIRE RANGE
包合電線断面積
0.5-1.25mm² (AWG #20-#16)

INSULATION DIA
被覆外径 2-2.6

DWN	T.SHINOHARA	27JUN01
CHK	K.BETSUI	27JUN01
APVD	K.BETSUI	27JUN01
PRODUCT SPEC	製品規格	
APPLICATION SPEC	取付適用規格	
WEIGHT	0.35 g	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: 単位: 耗 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差
0 PLC ±	1 PLC ±
2 PLC ±	3 PLC ±
4 PLC ±	ANGLES ±
FINISH 仕上	SEE TABLE 表参照
MATERIAL 材料	SEE TABLE 表参照

(GENERAL TOLERANCE)	
10mm	±0.25
30mm	±0.25
30mm	±0.3
角	±3°



TE Connectivity

ECONOSEAL J-MARKII CONNECTOR
TAB CONTACT

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	G171661	—

CUSTOMER DRAWING

SCALE 5:1 SHEET 1 of 1 REV E2