



NOTES

Available in 02 through 15 Circuits.
 Material : Nylon 66 UL94-V0(2).
 0.64mm Square Pin.
 Pin Material : Brass / Tin-Plated.

Circuits	Dimension mm			Circuits	Dimension mm		
	A	B	C		A	B	C
2	2.50	7.50	6.00	10	22.50	27.50	26.00
3	5.00	10.00	8.50	11	25.00	30.00	28.50
4	7.50	12.50	11.00	12	27.50	32.50	31.00
5	10.00	15.00	13.50	13	30.00	35.00	33.50
6	12.50	17.50	16.00	14	32.50	37.50	36.00
7	15.00	20.00	18.50	15	35.00	40.00	38.50
8	17.50	22.50	21.00	-	-	-	-
9	20.00	25.00	23.50	-	-	-	-

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1
				X.	±0.30	X°	±5°			CHKD	DATE
				.X	±0.20	.X°	±2°	APPD	PRODUCT NAME	2.50mm Crimp Style Connectors	
				.XX	±0.08	.XX°	±1°	VIEW	PART. NO.	SCALE	1:1
				.XXX	±0.03	.XXX°	±0.5°			DWG. NO.	009
A0	MODIFICATION		DATE								