


本公司智慧財產，未經同意不得複製  
DAILYWELL copyright, may not be used  
without permission from DAILYWELL



### SPECIFICATIONS

**MECHANICAL LIFE:** 100,000 make-and-break cycles.

**ELECTRICAL LIFE:** 50,000 cycles.

▲ **CONTACT RESISTANCE:** 200mΩ max. initial @2-4VDC 100mA

**CONTACT RATING:** 0.4Volt-Amps(VA) max.@20V max(AC or DC)

▲ **OPERATING POSITION:** 0.65±0.2mm.

▲ **OPERATING FORCE:** 630±130gf.

**INSULATION RESISTANCE:** 100MΩmin.

**DELECTRIC STRENGTH:** 1,000V RMS@sea level.


**OPERATING TEMPERATURE:** -30°C to 85°C .

**DEGREE OF PROTECTION :** IP67


**PANEL THICKNESS:** 1.5 mm (.059) min. - 5 mm (.197) max.

▲ **TORQUE:** 2.2 Nm max. applied to nut.

FUNCTION: momentary action






OFF




ON


SCHMATIC



PANEL MOUNTING



FCP-PY02x1/pce



MNU-PY01x1/pce

### MATERIAL

**HOUSING&BUSHING:** nylon 66

**BUTTON:** stainless steel

**ACTUATOR:** silicon

**TERMINAL/CONTACT:** Copper alloy ,with gold plated.

**RoHS & Lead Free**

德利威電子股份有限公司

DAILYWELL ELECTRONICS CO.,LTD.

SCALE(比例): 1:1

TOLERANCE (公差):  
0.00 mm ± 0.25mm  
0.0 mm ± 0.40mm

ANGULAR: ± 5°

FILE NAME : PY0001

TITLE  
圖名

Pushbutton Switches

SIZE  
圖紙

A4

DWG NO.  
圖號

PY063S2011X0M1R01

UNIT  
單位

inch  
mm

REV.  
版本

F

DATE  
日期

MAY - 22 - 2012

SHEET  
張數

1 of 1

CHECKED BY  
審核

陳燈財

DRAWN BY  
製圖

Dick

符號	原尺寸	修改後尺寸	變更日期
1 (A)	—	設計變更	AUG-03-2012
2 (B)	—	增加配件	AUG-15-2012
3 (C)	—	增加扭力值	MAY-23-2013
4 (D)	修正公差原±0.50[0.02]改為±0.25[0.01]		DEC-03-2015
5 (E)	PANEL THICKNESS原1.5~4mm修訂為1.5~5mm		FEB-24-2016