


ROHS COMPLIANT

REV.	DESCRIPTION	DATE	ECN NO.
01	NEW DESIGN	2019/03/30	-



No. of Contact	A ±0.25 A ±0.10	B ±0.13 B ±0.05	C ±0.38 C ±0.15	D ±0.25 D ±0.10
09	16.30	25.00	30.80	19.28

REMARKS:
MATERIALS AND FINISH
 SHELL : STEEL MATERIAL, FRONT NICKEL FINISHED
 BACK SHELL, TIN FINISHED
 INSULATOR : PBT THERMOPLASTIC, 30% GLASS
 FILLED, UL 94V-0 RATED
 CONTACT MATERIAL : BRASS
 CONTACT FINISH : FULL GOLD FLASH

ELECTRICAL CHARACTERISTICS
 CONTACT CURRENT RATING : 5.0 AMPS
 CONTACT RESISTANCE : 30 MILLIOHMS MAX
 DIELECTRIC WITHSTANDING VOLTAGE : 1000 V A.C MIN.
 INSULATION RESISTANCE : 5000 MEGOHMS MIN.
 TEMPERATURE RATING : -55°C ~ +105°C

DRAWN:	JEFF ZHOU	2019.03.30	东莞市赢海电子有限公司 D-SUB Solder Type(FEMALE)
CHECKED:	CHENG LIU	2019.03.30	
APPROVED:	JINGUO YANG	2019.03.30	
Dimensions in millimeters TOLERANCE UNLESS SPECIFIED: XX ± 0.13 Angles: ±2°		Code: 000 Scale: 1:1	TITLE:
		REV. 01	Part No.: GDR09F-180°