



PCB板安装尺寸

■ 技术参数 (SPECIFICATIONS)

- ◆ 额定电压: 100V AC DC  
Voltage rating: 100V AC DC
- ◆ 额定电流: 2.0A AC DC #24  
Current rating: 2.0A AC DC #24
- ◆ 耐压值: 800V AC/minute  
Withstand voltage 800V AC/minute
- ◆ 绝缘电阻: 1000MΩ MIN  
Insulation resistance: 1000MΩ MIN
- ◆ 接触电阻: 0.02Ω MAX  
Contact resistance: 0.02Ω MAX
- ◆ 工作温度: -25°C ~+85°C  
Working Temperature: -25°C ~+85°C
- ◆ 间距: 2.0 mm  
Pitch: 2.0 mm

■ 材料 (MATERIAL)

- ◆ 绝缘体: 尼龙9T  
Insulator: PA9T
- ◆ 接触针: 黄铜  
Contact PIN: Brass
- ◆ 焊片: 磷铜  
Solder tab: Phosphor bronze

孔数 尺寸	2A	3A	4A	5A	6A	7A	8A	9A	10A	11A	12A	13A	14A	15A	16A
A	2.0	4.0	6.0	8.0	10.0	12.0	14.0	16.0	18.0	20.0	22.0	24.0	26.0	28.0	30.0
B	4.7	6.7	8.7	10.7	12.7	14.7	16.7	18.7	20.7	22.7	24.7	26.7	28.7	30.7	32.7
C	8.0	10.0	12.0	14.0	16.0	18.0	20.0	22.0	24.0	26.0	28.0	30.0	32.0	34.0	36.0

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1
				X.	±0.30	X°	±5°			CHKD	DATE
				.X	±0.20	.X°	±2°	APPD	PRODUCT NAME	2.00mm Crimp Style Connectors	
				.XX	±0.08	.XX°	±1°	VIEW	PART. NO.	M2010VS-XX	
AO	MODIFICATION			DRAW	DATE	.XXX	±0.03	.XXX°	±0.5°	DWG NO.	009