




技术参数

1. 额定电流: DC30V 0.1A
2. 耐压: AC250伏 (50-60Hz) 持续1分钟
3. 接触电阻: 1欧max
4. 绝缘电阻: 100兆欧min . 500V DC.
5. 操作力: 180± 50gf.
6. 全行程: 2.0mm± 0.2mm.
7. 运行类型: 自锁/无锁
8. 寿命: 10,000次.



PCBLayout(pattern Side)

| NO. | Operating Type | Part No.    |
|-----|----------------|-------------|
| 1   | Push To Lock   | K8-5856S-L1 |
| 2   | Push No Lock   | K8-5856S-N1 |

|                |                |             |             |                           |                |              |
|----------------|----------------|-------------|-------------|---------------------------|----------------|--------------|
| ⑧              | Leaf spring    | —           | 2           | SUS                       | Natural        | —            |
| ⑦              | Terminal       | —           | 6           | Brass strip               | Plating silver | —            |
| ⑥              | Contact        | —           | 2           | Phosphor bronze           | Plating silver | —            |
| ⑤              | Spring         | —           | 1           | SUS                       | Natural        | —            |
| ④              | Base           | —           | 1           | Nylon                     | Gray           | —            |
| ③              | Crochet Needle | —           | 1           | SUS                       | Natural        | —            |
| ②              | Cover          | —           | 1           | POM                       | Black          | —            |
| ①              | KNOB           | —           | 1           | POM                       | White          | —            |
| ITEM           | PART NAME      | TER'NO.     | QTY.        | MATERIAL                  | FINISHING      | REMARK       |
| APPROVALS      |                | DATE        |             |                           |                |              |
| DRAWN          |                | J.X.Zhong   | 2018/08/01  | HROE ELECTRONICS CO.,LTD  |                |              |
| CHECKED        |                |             |             | TITLE: PUSHBUTTON SWITCHS |                |              |
| APPROVALS      |                |             |             | PART NO.                  |                |              |
| TOLERANCES ARE |                | 30~以上 ±0.30 | 10~30 ±0.20 | ANGLE ±2°                 | UNIT: mm       | SCALE: 1:1   |
|                |                | 5~10 ±0.15  | ~5 ±0.10    |                           | DRAWING NO.    | PROJ:        |
|                |                |             |             |                           |                | SHEET 1 OF 1 |

| ECN NO. | REV. | DATE. | DESCRIPTION. | CHANGE. | CHECK. | APPRO. |
|---------|------|-------|--------------|---------|--------|--------|
|         | A    |       | NEW          |         |        |        |