


A—A

B-B

C-C

1. MATERIAL: PHOSPHOR BRONZE, JIS C5191H, HV 200° ±5°
2. Along any Portion of strip, Max Allowable Camber is 0.04mm Per 1000mm Length .And MAX .Allowable Twist is 45 Per 1000mm Length.
3. All Corners and Radll have a maximum Radius of 0.1mm unless Otherwise Specified.

				TOLERANCE UNLESS OTHERWISE	DRAWN	CK tan	XFCN兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1
				X. ±0.30 X° ±5°	CHKD				DATE	2010.4.12
				.X ±0.20 .X° ±2°	APPD		PRODUCT NAME	3.96mm Crimp Style Connectors	UNITS	mm
A0				.XX ±0.08 .XX° ±1°					SCALE	1:1
VER	MODIFICATION	DRAW	DATE	.XXX ±0.03 .XXX° ±0.5°	VIEW		PART. NO.	T3960PS-2	DWG NO.	009