



额定负荷 Rating	DC 5V 0.1~5ml
接触电阻 Contact Resistance	≤500 mΩ
绝缘电阻 Insulation resistance	≥100M Ω
抗电强度 Dielectric strength	AC100V 50Hz/1min
操作力 Operation force	≤0.3N (31gf)
寿命试验 Operating Life	50000 cycles
行程 Travels	0.5±0.2



CIRCUIT DIAGRAM

P.C.B LAYOUT

NO.	PARTS	MATERIALS	QTY	FINISH
F	STAND	SPCC	1	Tin PLATED
E	THERMINAL	PHOSPHOR BRONZE	2	Ag PLATED
D	CONTACT SPRING	PHOSPHOR BRONZE	1	Ag PLATED
C	COVER	PA46	1	BLACK
B	CASE	PA46	1	BLACK
A	KNOB	PA46	1	WHITE

>0.5~2	±0.05	±0.10	±0.15
>2~5	±0.15	±0.20	±0.25
>5~10	±0.25	±0.28	±0.30
角度 ANGLE	±0.5°		

第一视角	设计 Jack Jin	图面单位 A4
	审核 Jacky Zhong	比例 1/1
	批准 Tony Meng	页码 1/1
		版次 A/0

东莞市美韩电子科技有限公司		DWG NO.	型号: UK-D0427-2	SIZE
Dongguan Usakro Electronic Technology Co., Ltd.		1 of 1	PART NO.	A4
未注尺寸公差 (mm)			规格: 6.4*4.6*5.23左	VIER
				R