



1. Rating : DC 30V,2.0A(12V,2.0A) ;
- 2.Contact resistance :  $\leq 30\text{m}\Omega$  ;
- 3.Insulation resistance :  $\geq 100\text{M}\Omega$  ;
- 4.Withstand voltage : 500VAC ;
- 5.Insertion and extraction force : 3-20N
- 6.life test : 5,000 cycles °



P. C. B LAYOUT  
TOP VIEW

MODEL NO.	
SCHEMATIC	
CENTER PIN	$\phi 2.0\text{mm}$
	$\phi 2.5\text{mm}$

NO.	DESCRIPTION	QTY	MATERIAL	PLATING
6	PIN	1	BRASS	Ni-Plating
5	FLAT FOOT	1	BRASS	Ag-Plating
4	CURVE PIECE	1	BRASS	Ag-Plating
3	SPRING PIECE	1	BRONZE	Ag-Plating
2	COVER	1	PART	
1	HOUSING	1	PART	

>0.5~2	$\pm 0.05$	$\pm 0.10$	$\pm 0.15$
>2~5	$\pm 0.15$	$\pm 0.20$	$\pm 0.25$
>5~10	$\pm 0.25$	$\pm 0.28$	$\pm 0.30$
角度 ANGLE	$\pm 0.5^\circ$		
未注尺寸公差(mm)			

第一视角	设计 Jack Jin	图面 单位	A4 MM	东莞市美韩电子科技有限公司 Dongguan Usakro Electronic Technology Co., Ltd.	
	审核 Jacky Zhong	比例 重量			
批准 Tony Meng	页码 版次	1/1 A/0	1:1	DWG NO.	型号: DC-050-2. 0-R
	1 of 1	PART NO.	规格: 9*11*14. 8/2. 0针/红色	SIZE A4	VER R