



CH1 A/R SWR MKR 3: 1.0922 U  
 REF 1.000 U 1.000U/ 1 350 000 000.HZ




CH1 START 000 000 000.HZ STOP 3 000 000 000.HZ

MAIN TECHNICAL SPECIFICATIONS

model	Type
FREQUENCY RANGE	0-3G
INPUT IMPEDANCE	50 OHM
VSWR	1:1.2
GAIN	----
POLARIZATION FORM	----
RADIATION	----
MAXIMUM POWER	----
CABLE	RF1.13-150MM
MAX DIAMETER	13.6mm
MIN DIAMETER	1.13mm
CONNECTOR TYPE	IPEX -- SMAKWE
LIGHTING PROTECTION	DC GROUNDING



深圳市金航标电子有限公司



技术详询

DWN BY/DATE JIANG 2015-03-25	DESG BY/DATE	TOLERANCE .X± .XX± .XXX± ANGLES±	SCALE 1 : 1		ENG PROJECT NO. KH 150325-0025	TITLE YL-IPEX-SMAKWE-RR1.13-150MM
CHK BY/DATE	APPD BY/DATE		UNIT m / m	SH 1 OF 1	CONTROL NO.	DWG NO. REV