


CATEGORY	DESCRIPTION	P/N #
CONNECTOR	RJ45 带壳沉板H=2.8mm(短脚)	MJ881A-BX11-HLRV2-X

料号由原 MJ881A-BX11-HLRV2
变更为 MJ881A-BX11-HLRV2-X

REV.	ECN NO	DESCRIPTION	REVISED	DATE
A01	—	New Release	XSY	2015.07.10
A02	—	新增包装选项	XSY	2016.05.06

8-0.40±0.05






X	Terminal Plating
0	G/F Plating
1	Au 3u" Plating
2	Au 6u" Plating
3	Au 15u" Plating
4	Au 30u" Plating


X	包装方式
C	卷带包装
P	吸塑盒包装

Part No.:
MJ881A-BX11-HLRV2-X

- SPECIFICATION
- VOLTAGE RATING: 125 VAC RMS.
 - CURRENT RATING: 1.5 AMP
 - CONTACT RESISTANCE: 40 mΩ MAX
 - INSULATION RESISTANCE: 500MΩ MIN.
 - WITHSTAND VOLTAGE:
AC1000V RMS 50Hz or 60Hz MIN.
 - OPERATING TEMPERATURE: -40°C~+80°C




Recommend PCB Layout
(Jack Top View)
Tolerance: ±0.05mm
Recommend PCB Thickness: 1.6mm



NO.	PART NAME	MATERIAL	QTY	REMARK
d	SHELL	BRASS T=0.2mm	1	
c	TERMINAL	PHOSPHOR BRONZE T=0.3mm	8	
b	COVER	LCP UL94V-0	1	
a	HOUSING	LCP UL94V-0	1	

UNLESS OTHERWISE SPECIFIED TOLERANCES

SCALE: 1/1 UNIT: mm
SIZE: A3 PAGE: 1 OF 1 REV: A02
DWG. NO: WI-061-149

 东莞市合陵电子有限公司
Dongguan Heling Electronic Co., LTD

DECIMALS:	ANGLES:	APPROVED BY	CHECKED BY	PREPARED BY
X : ±0.5	X : ±2°	DICK	XSY	XSY
XX : ±0.3	XX : ±1°	CUSTOMER COPY		
XXX : ±0.2				