

SPECIFICATIONS

Mechanical

Plug Mating Force: 4.50kgf max Plug Unmating Force: 1.00~4.00kgf

Durability: 10000 Cycles

Electrical

Current Rating: 0.50A min


Contact Resistance: $30m\Omega$ max change form initial Dielectric Withstanding Voltage: 500V AC RMS

Insulation Resistance: Unmated plug:100M Ω min at 500V DC

Mated plug:10M Ω min at 150V DC

Physical

Plating: See "ORDERING INFORMATION" **Operating Temperature:** -40 $^{\circ}$ to +85 $^{\circ}$




DisplayPort Connector

3VM Series

Mini DisplayPort,

DRAWING



ORDERING INFORMATION

