



PCB Layout (Pattern side)

NO.2	
PART NO	vigor
4	250±30

NO.3	
PART NO	MATERIAL/QTY
S	SUS/1PC

NO.4—NO.5	
PART NO	NOTE
01~99	SERIAL NUMBER

Typical Specifications :
 1. Rating : DC 12V 50mA
 2. Life:100,000 Cycles Min.



⑦	Gasket	—	1	Nylon	—	—	—
⑥	Waterproof Silicone	—	1	Silica gel	—	—	—
⑤	Terminal	—	4	Brass(0.3t)	Plating silver	—	—
④	Contact	—	1	F.Ag/SUS	—	—	—
③	Base	—	1	Nylon	Black	—	—
②	Cover	—	1	SUS	—	—	—
①	Keystroke	—	1	Nylon	Red	—	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK	—
APPROVALS		DATE	—				

DRAWN J.X.Zhong 2018/8/1

TITLE: TACT SWITCHS



CHECKED

PART NO. K2-1842DP-C4SW-□□

APPROVALS	30~80.0	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
TOLERANCES ARE	10~30	±0.20	±2°	DRAWING NO.	—	SHEET 1 OF 1
	5~10	±0.15				
	~5	±0.10				

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
—	A	—	NEW	—	—	—