

SPECIFICATIONS

Mechanical

Mating Force: initial 4.5kgf max. *Unmating Force:* initial 1.0~4.0kgf max. *Durability:* 10000 cycles.

Electrical Voltage Rating: 40V AC Current Rating: 0.5A . Contact Resistance: Initial excluding conductor resistance 10mΩ max. Dielectric Withstanding Voltage: 500V AC (Rms.)

Insulation Resistance: Unmated plug $100M\Omega$ min. at 500V DC.


Physical

Housing: Thermoplastic, UL 94V-0 rated in black Color **Contact:** Copper alloy **Plating:** See "ORDERING INFORMATION" **Solder Pad:** Copper alloy **Operating Temperature:** -40°C to +85°C

HDMI Receptacle Series Right Angle, TH Type 0.75mm [.030"] Pitch

19 Pos.

HDMI Connector



DRAWING

