

NOTE:  
 1.MATERIAL:  
 HOUSING:THERMOPLASTIC HIGH TEMPERATURE. COLOR-BLACK  
 CONTACT: COPPER ALLOY.  
 2.CONTACT FINISH:  
 CONTACT:80U" MIN TIN ,PLATED OVER 50U" MIN NICKEL PLATED  
 3.DIMENSIONAL :









P/N	POS	A	B	C	D
1-2834217-1	2	6.60	---	2.80	---
1-2834217-2	4	9.60	3.00	2.80	---
1-2834217-3	6	12.60	6.00	2.80	---
1-2834217-4	8	15.60	9.00	7.50	4.70
1-2834217-5	10	18.60	12.00	10.50	7.70
1-2834217-6	12	21.60	15.00	13.50	10.70
1-2834217-7	14	24.60	18.00	16.50	13.70
1-2834217-8	16	27.60	21.00	19.50	16.70
1-2834217-9	18	30.60	24.00	22.50	19.70
2-2834217-1	20	33.60	27.00	25.50	22.70
2-2834217-2	22	36.60	30.00	28.50	25.70
2-2834217-3	24	39.60	33.00	31.50	28.70

THIS DRAWING IS A CONTROLLED DOCUMENT. GEORGE FU 09DEC2016

INVENTOR: P/N	DESIGNED BY: SHI MING 09DEC2016	DATE: 09042016	BY: GF	APVD: SM
APPROVED BY: [Signature]	PRODUCT SPEC: 108-137257	SIZE: A2	CASE CODE: 00779	DRAWING NO: C-2834217
MATERIAL: [Symbol]	FINISH: [Symbol]	WEIGHT: [Symbol]	SCALE: 1:1	SHEET: 1 of 2

NOTE 1: [Symbol] NOTE 2: [Symbol]

STE TE Connectivity  
 MICRO FIT 3.0MM PITCH WAFER R/A TYPE  
 RESTRICTED TO: [Symbol]



DETAIL D

THIS DRAWING IS A CONTROLLED DOCUMENT. GEORGE FU 09DEC2016

INVENTOR: P/N	DESIGNED BY: SHI MING 09DEC2016	DATE: 09042016	BY: GF	APVD: SM
APPROVED BY: [Signature]	PRODUCT SPEC: 108-137257	SIZE: A2	CASE CODE: 00779	DRAWING NO: C-2834217
MATERIAL: [Symbol]	FINISH: [Symbol]	WEIGHT: [Symbol]	SCALE: 1:1	SHEET: 2 of 2

NOTE 1: [Symbol] NOTE 2: [Symbol]

STE TE Connectivity  
 MICRO FIT 3.0MM PITCH WAFER R/A TYPE  
 RESTRICTED TO: [Symbol]