

SWITCH FUNCTION

#### **SPECIFICATIONS**

MECHANICAL LIFE: 40,000 make-and-break cycles. CONTACT RATING: 0.4 VA max. @ 20 V AC or DC max.

CONTACT RESISTANCE: Below 100 m  $\Omega$  typ. initial @ 2-4 V DC, 100 mA.

INSULATION RESISTANCE: 500 M  $\Omega$  min.

DIELECTRIC STRENGTH: 500 Vrms min. @ sea level.

OPERATING TEMPERATURE: - 30°C to 85°C

## **MATERIALS**

HOUSING AND BASE:Glass filled nylon 6/6 or 4/6, flame retardant,heat stabilized(UL94V-0)

ACTUATOR: Glass filled nylon 6/6, flame retardant, heat stabilized(UL94V-0), with standard internal o-ring seal.

CONTACT: Phosphor bronze, with gold plated over nickel plated. (A)


TERMINALS:C2680, with gold plated over nickel plated.

TERMINAL SEAL:Epoxy.All terminals insert molded.

### **RoHS & Lead Free**

NOTE: Specifications and materials listed above are for switches with standard options.

For information on specific and custom switches, consult Customer Service Center.



PC MOUNTING

.100 2.54

# 蘇州寰立電子有限

							IACLEX E	LECTRO	INICS CC	)., LH	D.
	符號	原尺寸	修改後尺寸	變更日期	SCALE (比例): 1:1	TITLE	Sealed Ultramin	tton Switches	SIZE A4		
1	A		依N1119修訂夾片材質	JAN-29-2018		圖 名				圖紙	
1			[KITT 10][6][7][7][7]	5AIV 23 2010	TOLERANCE (公差):	DWG NO.	WG NO. 8UD8WR2C2			UNIT	inch
2	<u>B</u>				0.00 mm ± 0.25mm	圖 號	0000	/VRZUZIN	ZIVIZKES	單位	mm
3	(C)				0.0 mm ± 0.40mm	REV.	D DATE	OCT - 26	6 - 2010	SHEET	1 of 1
1	(D)				ANGULAR : ± 5°	版本	B 日期	001-20	0-2010	張 數	01 1
4					-	CHECKED BY	THE LOT BL	n   D	DRAWN BY	1054	
5	Œ				FILE NAME: 8UDP0024	審核	陳燈財		製圖	IREN	1F

版本: C 表單編號: QR-0507