



Specifications:

规格:
Voltage rating:30V AC/DC
 额定电压: 30V AC/DC
Current rating: 0.5A AC/DC
 额定电流: 0.5A AC/DC
Withstanding voltage:200V AC/minute
 耐压电压: 200V AC/分钟
Temperature range:-25℃~+85℃
 温度范围: -25℃~+85℃
Insulation resistance:≥100MΩ
 绝缘电阻: ≥100MΩ
Contact resistance: ≤20mΩ
 接触电阻: ≤20mΩ
After environment testing: ≤40mΩ
 环境试验后: ≤40mΩ

X0800 H 1 - XX X - N0 HF

① ②③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category: H-HSG
- ③ Welding Board Angle: I-HSG+hardware
- ④ Row No.-Pin No.: XX-Single row
- ⑤ Plug the Pin & Special No. G-Gold Plating
- ⑥ Material: N0-PA66 94V-0
- ⑦ HF-Halogen free

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
2	0.80	1.78	2.40	12	8.80	9.78	10.40
3	1.60	2.58	3.20	13	9.60	10.58	11.20
4	2.40	3.38	4.00	14	10.40	11.38	12.00
5	3.20	4.18	4.80	15	11.20	12.18	12.80
6	4.00	4.98	5.60	16	12.00	12.98	13.60
7	4.80	5.78	6.40	17	12.80	13.78	14.40
8	5.60	6.58	7.20	18	13.60	14.58	15.20
9	6.40	7.38	8.00	19	14.40	15.38	16.00
10	7.20	8.18	8.80	20	15.20	16.18	16.80
11	8.00	8.98	9.60				

X0800HI-XX-N0HF	Nylon 66 UL 94V-0 Halogen Free	AWG#32-36	0.39mm(Max)	Phosphor Bronze	Gold-Flash	X0800W
PART NO	Material	Suitable XKB Terminal	Insulation O.D	Material(Terminal)	Finish(Terminal)	

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: NA	MODEL TYPE:
DWNN	DATE	VIEW:	PART NO.: 0.80mm IDC Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g SHEET 1/1 REVISION A0