


## 晶创和立科技 GL75


## MINIATURE CADMIUM SULPHIDE PHOTOCONDUCTIVE CELL



## SPECIFICATION AND PERFORMANCE

Model	Vmax (VDC)	Pmax (mW)	Ambient temp(℃)	Spectral peak (nm)	Light Resistance at 10Lux (KΩ)	Dark Resistance (MΩ)	Gamm a value at 100- 10Lux	Response Time (ms)	
								Rise Time	Decay time
GL7516	150	100	-30~+70	540	5-10	0.5	0.7	20	30

## **Measuring Conditions**



SHENZHEN JINGCHUANGHELI TECHNOLOGY CO., L'Http://www.szjchl.comTel:+86-755-23210829Fax:+86-755-23210825E-mail:heli@szjchl.com