






RoHS



NOTE:

- 1.Rating: 50V 100mA DC
- 2.Insulation Resistance: ≥100 MΩ
- 3.Withstand voltage:AC 500V 1Minute
- 4.Operating Force Range: 500gf Max
- 5.Mechanical Life:3,000 Cycles

Ⓕ	Dust film		1	Polyimide tape	
Ⓖ	Terminal		2	Phosphor bronze	Gold plating
Ⓓ	Contact spring		1	Phosphor bronze	Gold plating
Ⓒ	Handle		1	PA46	White
Ⓑ	Cover		1	PPS	Black
Ⓐ	Base		1	PPS	Black
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co, Ltd
元迪

design	date	name	DIP SWITCH
Review	date	model	TP-01
Approved	date		

Drawing number: Proportion 1:1 unit mm gage number A4

modify Review Approved Tolerance not specified