





RoHS



NOTE:

- 1.Rating: 50V 100mA DC
- 2.Insulation Resistance: $\geq 100 \text{ M}\Omega$
- 3.Withstand voltage: AC 500V 1Minute
- 4.Operating Force Range: 500gf Max
- 5.Mechanical Life: 3,000 Cycles

Ⓕ	Dust film		1	Polyimide tape	
Ⓖ	Terminal		16	Phosphor bronze	Gold plating
Ⓓ	Contact spring		8	Phosphor bronze	Gold plating
Ⓒ	Handle		8	PA46	White
Ⓑ	Cover		1	PPS	Black
Ⓐ	Base		1	PPS	Black
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co, Ltd

design	date	name	DIP SWITCH
Review	date	model	TP-08
Approved	date		

Drawing number: A4

modify Review Approved

Tolerance not specified

Proportion

1:1

unit

mm

gape number