



300V 12A 26-14AWG 1.5mm²

Poles: 2P&3P-24P

Pitch: 5.0mm (.197")

Materials

Housing: PA66 (UL 94V-0)

Wire Cage: Brass, Nickel plated

Solder Pin: Brass, Tin Plated

Screw: M3, Steel, Zinc Plated

Torque: 0.5N.m

设计/Designed by	绘图/Drawing by	审核/checked by	批准/Approved by	公差/General Tolerance
				x. ±0.2 x. ±0.1 .xx ±0.05 .xxx ±0.01
新莱亚电子 XINLIYI ELECTRONIC CO., LTD		图名/Title	文件编号/Title No.	x. ±2° x. ±1° .xx ±0.5° .xxx ±0.5°
		备注/Remark	页序/Sheet	单位/units: 张

序号/Revno. 更改记录/Revision record

签名/Signature

日期/Date