



300V 15A 22-14AWG 1.5mm²
Poles: 2&3-24P
Pitch: 5.0mm (.197")/5.08mm (.200")
Materials
Housing: PBT (UL 94V-0)
Wire Protector: Stainless Steel
Solder Pin: Brass, Tin Plated
Screw: M2.5, Steel (A3), Zinc Plated
Torque: 0.4N.m

序号/revno.: 更改记录/revision record
 签名/signature 日期/date

设计/Designed by	绘图/Drawn by	审核/checked by	批准/Approved by	公差/公差 General Tolerances
				X. ±0.2 X. ° ±2° .X ±0.1 .X' ±1° .XX ±0.05 .XX' ±0.5° .XXX ±0.01
新莱亚电子 XINLADYA ELECTRONIC CO., LTD		图名/Title	文件编号/Title No.	
		XY301R-A		
		-B	页序/Sheet	
			单位/units: 数量	