



### 技术参数 SPECIFICATIONS

- 线数 (Poles) : 2、3、4、6、9
- 适用线规 (Applicable wires) : AWG22#~18#
- 温度范围 (Temperature range) : -25℃~85℃
- 额定电压 (Voltage rating) : 300V.Ac/Dc
- 额定电流 (Current rating) : 10A
- 接触电阻 (Contact resistance) : ≤0.01Ω
- 绝缘电阻 (Insulation resistance) : ≥1000MΩ
- 耐压 (Withstand voltage) : 1200V.Ac/1min
- 材料 (Material) :  
 插头 (Plug housing) : 尼龙 (PA66) UL94V-2(0)  
 插座 (Receptacle housing) : 尼龙 (PA66) UL94V-2(0)  
 端子 (Terminal) 黄铜 (Brass Tin/plated)

### 端子 TERMINAL

型号 Type	适用线规 Applicable wires		电线外径 O.D of wire ins mm	数量 Quantity
	mm <sup>2</sup>	AWG#		
HX28050-PT	0.33~0.82	22~18	1.7~3.0	4000PCS/盘
HX28050-RT	0.33~0.82	22~18	1.7~3.0	3000PCS/盘

线数 (Poles)	额定电压 (Voltage rating)	额定电流 (Current rating)	插头 (Plug housing)		插座 (Receptacle housing)	
			型号	尺寸图	型号	尺寸图
			HX28050-PT(DJ621-E2.8x0.5A-B)		HX28050-RT(DJ611-2.8x0.5A-B)	
2	300V	10A	HX28050-2P(DJ7021A-2.8-21)		HX28050-2R(DJ7021A-2.8-11)	
3	300V	10A	HX28050-3P(DJ7031A-2.8-21)		HX28050-3R(DJ7031A-2.8-11)	
4	300V	8A	HX28050-4P(DJ7041A-2.8-21)		HX28050-4R(DJ7041A-2.8-11)	
6	300V	8A	HX28050-6P(DJ7061A-2.8-21)		HX28050-6R(DJ7061A-2.8-11)	
9	300V	8A	HX28050-9P(DJ7091A-2.8-21)		HX28050-9R(DJ7090A-2.8-11)	