


SCHMATIC



额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	160±30gf → 250±50gf
寿命试验 Operating Life	100,000 cycles 70,000 cycles
行程 Travels	0.25±0.1mm

NO.	Name	Number	Qty	Material	Remarks
⑤	Terminal	4		Brass	Silvering
④	Reed	1		Phosphorus copper	Silver covered
③	Base	1		PPA	Black
②	Cover	1		SPCC	Nickel Plating
①	Keystoke	1		PPA	Black

数量	公差	公差	公差
0~3	±0.05	±0.10	±0.20
>3~6	±0.05	±0.10	±0.30
>6~30	±0.10	±0.20	±0.50
>30~120	±0.15	±0.30	±0.80

未注尺寸公差 (mm)

第一视角	设计 Jack Jin	图面 单位 A4 MM	东莞市美韩电子科技有限公司 Dongguan Usakro Electronic Technology Co., Ltd.		
	审核 Jacky Zhong	比例 重量	1:1	DWG NO.	型号: UK-B0219-TP-250
	批准 Tony Meng	页码 版次 1/1 A/0	1 of 1	PART NO.	规格: 6*6*7.3方头 贴片

SIZE	A4
VER	R