


REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE




VIEW A

2EDGVC - 5.0/5.08 - XXP - 1Y - 00A (H)

(Series No.) (Pitch) (Poles)(Single Pitch) (Color)

(RoHS)  
00A- (Standard)

- (Grey)
- (Blue)
- (Black)
- (Green)
- (Orange)
- (Red)
- (Transparent)
- (Yellow)
- (White)



NOTES1:

- UL Standard
- 1. Rated voltage/current : 300V / 15A
- 2. Withstanding voltage : AC1600V/1Min.

IEC Standard


Pollution degree	2
Overvoltage category	III
Rate impulse voltage(KV)	4.0KV
Rate voltage(V)	320V
Rate current(A)	20A

NOTES2:



- Dimension shall be interpreted per ASME Y14.5-2009
- Pitch : 5.0/5.08mm, Poles : N=02~24P
- Operating temperature: -40°C~+105°C
- Undimensioned tolerances:

Pitch range in mm		Nominal dimension range in mm						∓	∅
Over 6 TO 10	Over 10 TO 24	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150	Over 150 TO 300	Over 300 TO 600	0.1/10	<	
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2'	

5. RoHS Compliance



1.00



PCB LAYOUT

DETACHED LISTS	PART NO.:	/		
	APPD:	/		
	CHKD:	/		
	DRFT:	/		
	<p>THIRD ANGLE PROJECTION</p>		<p>DO NOT SCALE DRAWING</p>	
<p>NINGBO DEGSON ELECTRICAL CO., LTD</p>		<p>NAME: 2EDGVC-5.0/5.08-XXP-1Y-00A(H)</p>		
TITLE: CUSTOMER DRAWING		REV	DO	
DRAWING NO.:		SHEET	1/1	
MM (INCH)		SCALE	1:1	