



SPECIFICATION

Contact Rating : 50mA, 12V DC
 Contact Resistance : 100mΩ max
 Insulation Resistance : 100mΩ min. 500V DC
 Dielectric Strength : 250V AC/1minute
 Travel : 0.25mm
 Operating Temp : -20 °C ~ +70 °C
 Storage Temp : -30 °C ~ +80 °C



PCB. WELDING DRAWING



CIRCUIT DIAGRAM

Code-X	H
A	4.3
B	4.8
C	5.0
D	5.3
E	5.5
F	6.0

PAPT NO	TC-1101DE-X-X
Operating Force	B: 160gf C: 260gf
Height	Code-X

ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	2	Brass (0.30t)	Plating silvering	—
④	Contact	—	1	F.ag/Sus	Natural	—
③	Base	—	1	LCP	—	—
②	Cover	—	1	Spcc	Plating Nickel	—
①	Keystake	—	1	Pa46	—	—

MARK	DESCRIPTION	DATE	REVISED	APPROVED	units: mm	DSND	DATE	SCALE: N/A	MODEL TYPE:		
Δ X					tolerance: X.X ±0.2mm	DWN	DATE	VIEW:	TACT SWITCH		
Δ X					X.XX ±0.1mm	CHKD	DATE	UNIT: mm	PART NO.:		
Δ X					X.XXX ±0.05mm	APPD	DATE	SIZE: A4	DWG NO.:		
						UNSPECIFIED TOLERANCES			TC-1101DE-X-X		
www.xk-dg.cn www.helloxkb.com www.helloxkb.com						XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g	SHEET 1/1	REVISION A0