
## KEMET Part Number: PMR209MB5470M100R30

(P409QM473M250AH101)



PMR209, Film, Metallized Paper, Resistor/Capacitor, 0.047 uF, 20%, 630 VDC, 85°C, Lead Spacing = 15.2mm



Dimensions		
L	18.5mm MAX	
Н	13mm MAX	
Т	7.3mm MAX	
S	15.2mm +/-0.4mm	
LL	30mm +5mm	
F	0.8mm +/-0.05mm	

Packaging Specifications		
Packaging:	Bulk, Bag	
Packaging Quantity:	400	

General Information	
Series:	PMR209
Dielectric:	Metallized Paper
Style:	Radial
Features:	RC Unit approved
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	ENEC, UL, cUL
AEC-Q200:	No
Construction:	Molded
Miscellaneous:	Resistor= 100 Ohms.
Notes:	Not For New Design, Please Use The New P409 Series @ 275 VAC.

Specifications		
Capacitance:	0.047 uF	
Capacitance Tolerance:	20%	
Voltage AC:	250 VAC	
Voltage DC:	630 VDC	
Temperature Range:	-40/+85°C	
Rated Temperature:	85°C	
Insulation Resistance:	3 GOhms	
Safety Class:	X2	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

