






RoHS



Circuit Diagram



PCB Layout(Pattern side)



Technical Parameters

- 1. Rated current: DC 30V 0.1A
- 2. Operating force: 50±10gf
- 3. Mechanical life: 50,000 times

NO.	Name	Number	Qty	Material	Remarks
(F)	Terminal		2	Brass	Silvering
(D)	Contact spring		1	Phosphor bronze	Silvering
(C)	Button		1	POM	Black
(B)	Cover		1	POM	Black
(A)	Base		1	PA66	Black

YUANDI® Yuandi Electronics Co., Ltd

design	date	name	DETECTION SWITCH
Review	date	model	TQ-2533A
Approved	date		

Drawing number: Proportion: 1:1 unit: mm gage number: A4

modify Review Approved Tolerance not specified

angle	±2'
10~30	±0.30
5~10	±0.20
~ 5	±0.10