






RoHS



PCB Layout(Pattern side)



Technical Parameters

- 1.Rated current: DC 30V 0.1A
- 2.Operating force:50±10gf
- 3.Mechanical life: 50,000 times

(F)	Spring		1	SUS	Natural
(E)	Terminal		2	Brass	Silvering
(D)	Contact Reed		1	Phosphor bronze	Silvering
(C)	Button		1	POM	Black
(B)	Cover		1	POM	Black
(A)	Base		1	PA66	Black
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co.,Ltd

design	date	name	DETECTION SWITCH
Review	date	model	TQ-2533
Approved	date		

Drawing number: A4

angle	±2'
10~30	±0.30
5~10	±0.20
~ 5	±0.10

modify Review Approved Tolerance not specified

Proportion 1:1 unit mm gage number