




环保物料

TEL: 0769-82001899



Color	Wire size
Orange	#18
Yellow	#20
Red	#22
White	#24
Blue	#26
Jblack	通用型

◆ SPECIFICATIONS
 Current rating: 7A AC, DC
 Voltage rating: 250V AC, DC
 Temperature range: -25°C ~ +85°C
 Insulation resistance: 1000MΩ Min.
 Withstanding voltage: 1500V AC/ minute.
 Contact resistance: 20m Ω Max.



PART No.	Dimension	
	A	B
02	3.96	7.92
03	7.92	11.88
04	11.88	15.84
05	15.84	19.80
06	19.80	23.76
07	23.76	27.72
08	27.72	31.68
09	31.68	35.64
10	35.64	39.60
11	39.60	43.56
12	43.56	47.52
13	47.52	51.48
14	51.48	55.44
15	55.44	59.07

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1	
				X.	±0.30	X°	±5°			CHKD	DATE	2010. 4. 12
				.X	±0.20	.X°	±2°	APPD	PRODUCT NAME	3.96mm IDC Style Connectors		
				.XX	±0.08	.XX°	±1°	VIEW	PART. NO.	M7060R-XX-XXX		
A0 VER	MODIFICATION		DRAW	DATE	.XXX	±0.03	.XXX°	±0.5°	UNITS			mm
									SCALE		1:1	
									DWG NO.		009	