



特性:Specifications

电气:Electrical:

1. 接触阻抗:Contact Resistance
30 milliohms MAX
2. 耐电压:Dielectnic Withstanding Voitage:
500 V AC AT Sea Level
3. 绝缘阻抗:Insulation Resistance:
1000MEGA ohms MIN

机构:Mechanical:

1. 结合为:Mating Force:
4.0KG NAX 最大4kg
2. 拔出力:Unmating Force:
0.5 KG NIN 最少0.5kg

材料:Material:

1. 塑胶:Housing:Hing Temperature Thermaplastio
2. 端子>Contact:Copper Alloy 铜合金
3. 外壳:Shell: Copper Aiioy铁/铜合金

电镀:Finish:

1. 端子>Contact: Plated Gold in Mating Area;
Tin On Solder Talis
接触点镀金. 脚镀锡
2. 外壳:Shell:

Nickel Plating 镀镍

>0.5~2	±0.05	±0.10	±0.15
>2~5	±0.15	±0.20	±0.25
>5~10	±0.25	±0.28	±0.30
角度 ANGLE	±0.5°		
未注尺寸公差(mm)			

第一视角



设计 Jack Jin	图面 单位 MM	A4	东莞市美韩电子科技有限公司 Dongguan Usakro Electronic Technology Co., Ltd.			
审核 Jacky Zhong	比例 重量		1:1	DWG NO.	型号: UK-USB AF 90度双层	SIZE A4
批准 Tony Meng	页码 版次	1/1 A/0	1 of 1	PART NO.	规格: 17.3*15.5卷边弯脚	VER R