





RoHS





短柄 Short handle



PCB Layout(Pattern Side)



Circuit Diagram



凸柄 Convex handle

NOTE:

1. Rating: 24V 25mA DC
2. Insulation Resistance: $\geq 100 \text{ M}\Omega$
3. Withstand voltage: AC 500V 1Minute
4. Operating Force Range: 500gf Max
5. Mechanical Life: 3,000 Cycles

Number of digits(位数)	1P	2P	3P	4P	5P	6P	7P	8P	9P	10P	12P
Cover/black 凸柄 盖子/黑色	TL-01	TL-02	TL-03	TL-04	TL-05	TL-06	TL-07	TL-08	TL-09	TL-10	TL-12
短柄	TL-01D	TL-02D	TL-03D	TL-04D	TL-05D	TL-06D	TL-07D	TL-08D	TL-09D	TL-10D	TL-12D

NO.	Name	Number	Qty	Materil	Remarks
Ⓔ	Terminal	16		Brass	Gold plating
Ⓓ	Shrapnel	8		Beryllium copper	Gold plating
Ⓒ	Handle	8		PA46	White
Ⓑ	Cover	1		PPS	Black
Ⓐ	Base	1		PPS	Black

YUANDI® Yuandi Electronics Co, Ltd

design	date	name
Review	date	DIP SWITCH
Approved	date	model
Drawing number:		TL-08