






RoHS




短柄 Short handle



PCB Layout(Pattern Side)



凸柄 Convex handle



Circuit Diagram

NOTE:

- 1.Rating: 24V 25mA DC
- 2.Insulation Resistance: $\geq 100 \text{ M}\Omega$
- 3.Withstand voltage: AC 500V 1Minute
- 4.Operating Force Range: 500gf Max
- 5.Mechanical Life: 3,000 Cycles

Number of digits(位数)	1P	2P	3P	4P	5P	6P	7P	8P	9P	10P	12P
Cover/black 凸柄 盖子/黑色 短柄	TL-01	TL-02	TL-03	TL-04	TL-05	TL-06	TL-07	TL-08	TL-09	TL-10	TL-12
	TL-01D	TL-02D	TL-03D	TL-04D	TL-05D	TL-06D	TL-07D	TL-08D	TL-09D	TL-10D	TL-12D

Ⓔ	Terminal		24	Brass	Gold plating
Ⓓ	Shrapnel		12	Beryllium copper	Gold plating
Ⓒ	Handle		12	PA46	White
Ⓑ	Cover		1	PPS	Black
Ⓐ	Base		1	PPS	Black
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co., Ltd
元迪

design	date	name	DIP SWITCH
Review	date	model	TL-12
Approved	date		

Drawing number: Proportion 1:1 unit mm gage number A4

modify Review Approved Tolerance not specified

angle $\pm 2'$
10~30 ± 0.30
5~10 ± 0.20
~ 5 ± 0.10