


REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			



NOTES:

1. ELECTRICAL:
 - 1.1. VOLTAGE RATING:DCV 300V 10MS
 - 1.2. CONDUCTANCE RESISTANCE:3.0 OHMMAX.
 - 1.3. INSULATION RESISTANCE:5.0M OHM/MIN.
 - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
 - 2.1. SEE TABLE
3. ALL COMPONENTS ARE ROHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	黑色热缩套管, OD:2.0MM	AS
③	端子	高仿IPEX 0.81 4代端子, 镀金	1
②	接头	SMA母头母针, 分体, 11牙, 镀金	1
①	同轴线	RF 0.81线材,颜色: 黑色, OD:0.81mm	AS

金航标电子有限公司

ALL DIMENSION
ARE IN MM

DRAWN Jany DATE 2020-06-18

COMPUTER GENERATED
IN SOLIDWORKS

ENG.

DO NOT SCALE
THIS DRAWING

M.F.G.

PROJECTION

Q.A.

GENERAL TOLERANCE FOR
ANGLES X.X X.XX X.XXX

± 1° ± 0.3 ± 0.25 ± 0.150

I-PEX 0.81 4代 TO SMA /F L= 80mm

SIZE Number

B

REV

A

SCALE: Free

TYPE

SHEET 1 OF 1

技术详询

CUSTOMER P.N.:

