



Specifications:
IMPEDANCE: 50 Ohms
Frequency range: 0~6GHz
VSWR: 1.5MAX
Working voltage: 500V rms @ sea level
Insulation resistance: 5000 Ohms min
Temperature range: -55°C T0 +155°C
Relative temperature: ≤95% (40° C±2° C)

1	Body	Brass	Au:In ⁺	NOTE:					
2	Insulator	TEFLON	White						
3	Center contact	Phosphor	Au:3u ⁺						
4				DRAWN					
5				Zelin Zhang					
6				CHECKED					
7									
8									
9									
10	Component Number	Material	Finish	APPROVALS		SCALE			
A				<i>Johs Kline</i>		1:1			

Product NO.		DOSIN-806-0100		
REV	DESCRIPTION	DWN	DATE	APPROVEN
A	First Issue	Mr. Kang	2015/07/03	Johs Kline

DOSIN *Industrial (HK) Co Ltd* E-mail: dosin2006@163.com
 东莞市松山湖五金电子有限公司 dosin2006@dosin-hk.com
 Dosin Hardware Electronics Co, Ltd TEL: (0086) 769-81153906
 Name: SMA Jack Right angle PCB Mount FAX: (0086) 769-81578836

DATE: 2015/07/03
 Product NO. DOSIN-806-0100
 CAD FILE H/company drawings/BD
 SHEET: 1 OF 1