

**HSF** RoHS






**SPECIFICATIONS**

Rated(额定参数): 300V,7A  
 Dielectric strength(抗电强度): AC2000V/1 Minute  
 Insulation Resistance(绝缘电阻):1000MΩ Min  
 Contact Resistance(接触电阻):20mΩ Max  
 Wire Range(线径):24~20AWG  
 Strip length(剥线长度):8.5~9.5mm  
 Temp. range(操作温度): -40℃~+105℃  
 MAX Soldering(瞬时温度):+250℃,5s

Housing Material(塑件): PA66 (UL94 V-0)  
 Contact(端子): Brass, Tin plating(黄铜镀锡)

PITCH RANGE IN MM			NOMINAL DIMENSION RANGE IN MM				
TO	OVER	OVER	TO	OVER	OVER	OVER	OVER
6	6 TO 10	10 TO 24	30	30 TO 60	60 TO 100	100 TO 150	150
±0.10	±0.15	±0.25	±0.30	±0.30	±0.50	±0.70	±1.00


Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



**Ordering Information**

**JL250 A - 250 XX X X 1**

A=A-Type    Pitch 250=2.5PH    No.of pins 2P~24P    Housing Color B=Black G=Green U=Blue R=Red W=White Y=Yellow O=Orange E=Grey    Packing 0=Pe bag T=Tube A=Tray



				OPERATION		DRAW	yiyusheng	19.07.16	SCALE	FIT	<b>JILN</b> ® 深圳市锦凌电子有限公司 SHENZHEN JINLING ELECTRONIC CO.,LTD Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992	
				X.X	±0.30				UNIT	mm		
						CHECK			SIZE	A4	PART NO.	JL250A-250XXXX1
				X.XX	±0.20		SHEET	1/1	TITLE:	2.5mm Spring Terminal Blocks		
				X.XXX	±0.10	APPROVE			PROJ.			
A0	2019.07.16	NEW DRAWING		Angle	±3°							
REV	DATE	MODIFICATION DESCRIPTION		DIM	TOL							