



**Specifications :**

- Voltage rating: 350V AC / DC
- Current rating: 4 A AC / DC
- Withstanding voltage: 1700V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤30mΩ
- After environmental testing: ≤20mΩ

X1800 H X-02 A-N0  
 ① ②③ ④⑤ ⑥

- ① Series No.
- ② Category: H-HSG
- ③ Welding Board Angle: Blank-ordinary
- ④ Row No.-Pin No.: 02-02P
- ⑤ Plug the Pin & special No.: A- NO Lock
- ⑥ Material: N0-PA66 94V-0

X1800H-02A-N0	Nylon 66 UL 94V-0	X1800T	X1800W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

For and on behalf of  
**XKB INDUSTRIAL PRECISION CO., LIMITED**  
**香港星坤工業精密有限公司**

△ X					ANGULAR	±5°
△ X					L ≤ 4	±0.2
△ X					4 < L ≤ 16	±0.3
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4
					L > 63	±0.5
					REVISIONS	UNSPECIFIED TOLERANCES

DSND		DATE		SCALE: N/A	MODEL TYPE: X1800H-02A-N0
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm	1.80mm Crimp Style Connectors
APPD		DATE		SIZE: A4	DWG NO.:
<b>XKB INDUSTRIAL PRECISION CO., LIMITED</b>					WEIGHT
					1.0g
					SHEET
					1/1
					REVISION
					A0

*Authorized Signature(s)*