



NOTES:

- MATERIAL:
- 1. HOUSING MATERIAL : GLASS FILLED POLYESTER UL94V-0.
 - 2. CONTACT MATERIAL : PHOSPHOR BRONZE t=0.30mm
 - 3. PLATING : SELECTING GOLD PLATING 3u"~50u" OVE NICKEL

ELECTRICAL:

- 1. VOLTAGE RATING : 125 VAC RMS.
- 2. CURRENT RATING : 1.5 AMP.
- 3. CONTACT RESISTANCE : 30 MILLIOHMS MAX
- 4. INSULATION RESISTANCE : 500 MEGOHMS MIN @500V DC.
- 5. DIELECTRIC WITHSTANDING RESISTANCE : 1000V AC RMS 50Hz 1MIN

MECHANICAL:

- 1. DURABILITY : 750 CYCLES MIN.
 - 2. PCB RETENTION PRE-SOLDER : 1 LB MIN.
- ENVIRONMENTAL:
- 1. STORAGE : -40° C TO 85° C.
 - 2. OPERATION : 0° C TO 70° C.

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:
CHECKED:	DATE:
DRAWN:	DATE:
LYP	2011-01-13

		深圳市灿科盟实业有限公司 CHANTW CHANKLEMENT INDUSTRY CO., LTD	
TITLE: 网口插座			
RJ45-8P/8C 1x2 双线路 直插 带屏蔽 无灯 无弹片			
PART. NO.	R-RJ45S08P-B200	UNIT	mm
SCALE	free	SCALE	free
FILE NO.	Chantw-RJ45-0031	REV.	A HY04