






Temperature -20~70C
 Rated Load DC30V 0.3A
 Contact Resistance <0.03
 Insulation Resistance >100M
 Withstand Voltage AC500V(50Hz)/min
 Actuating Force 2.2~30N
 Life 3000N



PIN	PJ-359H-X	
Schematic		B:Black W:White

	MATERIAL	PLATING
termina 1	Phosphor Bronze	ag
termina 2	Phosphor Bronze	ag
termina 3	Phosphor Bronze	ag
termina 4	Phosphor Bronze	ag
terminal 5	Phosphor Bronze	ag
terminal 6	Phosphor Bronze	ag
Plastic	PA66	
Plastic	Pom	
base	PBT	

REVISIONS					UNSPECIFIED TOLERANCES	DSND	DATE	SCALE: N/A	MODEL TYPE: 3.5 PHONE JACK
ΔX					ANGULAR ±5°	DWN	DATE	VIEW:	PART NO.:
ΔX					X.X ±0.2mm	CHKD	DATE	UNIT: mm/in	DWG NO.: PJ-359
ΔX					X.XX ±0.1mm	APPD	DATE	SIZE: A4	
MARK	DESCRIPTION	DATE	REVISED	APPROVED	X.XXX ±0.05mm	XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT SHEET REVISION 1.0g 1/1 A0