



P.C.B Layout (copper-sided view)



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3~20N
 Operating Life:5,000cycles

Model NO	PJ-380B-A	PJ-380B-B
	PJ-380B-C	PJ-380B-D
Schematic		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHECK.	APPRO.																																																																
	A		NEW																																																																		
<table border="1"> <tr> <td>② Terminal</td> <td>4</td> <td>Phosphor bronze</td> <td>Au Plating</td> </tr> <tr> <td>① Housing</td> <td>1</td> <td>Nylon</td> <td>Black</td> </tr> <tr> <td>ITEM</td> <td>PART NAME</td> <td>TER'NO.</td> <td>QTY.</td> <td>MATERIAL</td> <td>FINISHING</td> <td>REMARK</td> </tr> <tr> <td colspan="2">APPROVALS</td> <td>DATE</td> <td colspan="4"></td> </tr> <tr> <td>DRAWN</td> <td>J.X.Zhang</td> <td>2013/11/11</td> <td colspan="4">ELECTRONICS CO.,LTD</td> </tr> <tr> <td>CHECKED</td> <td></td> <td></td> <td colspan="4">TITLE: PHONE JACKES</td> </tr> <tr> <td>APPROVALS</td> <td></td> <td></td> <td colspan="4">PART NO. PJ-380B</td> </tr> <tr> <td colspan="2">TOLERANCES ARE</td> <td>30^{+0.15}_{-0.10}</td> <td>±0.30</td> <td>ANGLE</td> <td>UNT: mm</td> <td>SCALE: 1:1</td> </tr> <tr> <td></td> <td></td> <td>5^{+0.15}_{-0.10}</td> <td>±0.10</td> <td>±2°</td> <td>DRAWING NO.</td> <td>PROJ-</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td>SHEET 1 OF 1</td> </tr> </table>						② Terminal	4	Phosphor bronze	Au Plating	① Housing	1	Nylon	Black	ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK	APPROVALS		DATE					DRAWN	J.X.Zhang	2013/11/11	ELECTRONICS CO.,LTD				CHECKED			TITLE: PHONE JACKES				APPROVALS			PART NO. PJ-380B				TOLERANCES ARE		30 ^{+0.15} _{-0.10}	±0.30	ANGLE	UNT: mm	SCALE: 1:1			5 ^{+0.15} _{-0.10}	±0.10	±2°	DRAWING NO.	PROJ-							SHEET 1 OF 1
② Terminal	4	Phosphor bronze	Au Plating																																																																		
① Housing	1	Nylon	Black																																																																		
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK																																																															
APPROVALS		DATE																																																																			
DRAWN	J.X.Zhang	2013/11/11	ELECTRONICS CO.,LTD																																																																		
CHECKED			TITLE: PHONE JACKES																																																																		
APPROVALS			PART NO. PJ-380B																																																																		
TOLERANCES ARE		30 ^{+0.15} _{-0.10}	±0.30	ANGLE	UNT: mm	SCALE: 1:1																																																															
		5 ^{+0.15} _{-0.10}	±0.10	±2°	DRAWING NO.	PROJ-																																																															
						SHEET 1 OF 1																																																															