


P.C.B LAYOUT(copper-sided view)



Model No.	PJ-3280A-A	PJ-3280A-B	PJ-3280A-C
Schematic			

Model No.	PJ-3280A-D	PJ-3280A-E
Schematic		

Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
<p>DRAWN J.X.Zhang 2013/11/11</p> <p>CHECKED</p> <p>APPROVALS</p> <p>TOLERANCES ARE 30%以上 ±0.30 ANGLE 30°~90° ±0.20 5°~10° ±0.15 ±2°</p>						
TITLE: PHONE JACKES			PART NO. PJ-3280A			
DRAWN J.X.Zhang 2013/11/11			DATE			
ELECTRONICS CO.,LTD			MATERIAL Nylon			
PHOSPHOR BRONZE Au Plating			FINISHING Black			
5			REMARK			
1			UNIT: mm			
SCALE: 1:1			DRAWING NO.			
PROJ			SHEET 1 OF 1			