


P.C.B LAYOUT(copper-sided view)



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

Model No.	PJ-3910-A	PJ-3910-B	PJ-3910-C
Schematic			
	PJ-3910-D	PJ-3910-E	

② Terminal	6	Phosphor bronze	Au Plating
① Housing	1	Nylon	Black
ITEM PART NAME	TERN.O.	QTY.	MATERIAL FINISHING
APPROVALS		DATE	REMARK
DRAWN	J.X.Zhang	2013/11/11	
CHECKED			
APPROVALS			
TOLERANCES ARE	30 ^{±0.15}	±0.30	ANGLE
	10 ^{±0.20}	±0.20	UNIT: mm
	5 ^{±0.10}	±0.15	SCALE: 1:1
	~ 5	±0.10	DRAWING NO.
			PART NO. PJ-3910
			TITLE: PHONE JACKES
			ELECTRONICS CO.,LTD
			PROJ. SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			