





3D VIEW

NOTES:



1. CONTACT CURRENT RATING: 1A.
2. CONTACT RESISTANCE: 50 mΩ MAX.;
3. INSULATION RESISTANCE: 1000MΩ MIN.;
4. DIELECTRIC WITHSTANDING: 500V AC MIN.;
5. DURABILITY: 5,000 CYCLES MIN.;
6. CONNECTOR MATING FORCES: 30N MAX.;
7. CONNECTOR UNMATING FORCES: 3N MIN.;



P.C.B LAYOUT TOP VIEW 正贴



P.C.B LAYOUT TOP VIEW 反贴



| | | | | | | |
|-----------|-----------|------------|---------------------|-------------------------|---|---|
| ② | Terminal | 6 | SUS/Phosphor bronze | Au Plating | | |
| ① | Housing | 1 | Nylon | Black | | |
| ITEM | PART NAME | TER'NO. | QTY. | MATERIAL | FINISHING | REMARK |
| APPROVALS | | DATE | | ELECTRONICS CO.,LTD | | |
| DRAWN | LIUCAN | 2022.11.12 | | | | |
| CHECKED | | | | PART NO. | PJ-399F-6A | |
| APPROVALS | | | | TOLERANCES ARE | 30~以上: ±0.30 10~30: ±0.20 5~10: ±0.15 ~ 5: ±0.10 | ANGLE: ±2' UNIT: mm SCALE: 1:1 PROJ: |
| ECN NO. | REV. | DATE. | NEW DESCRIPTION. | CHECK. | APPRO. | SHEET 1 OF 1 |